

Plug socket MSSD-C-S-M16

Part number: 192748

FESTO



Data sheet

Feature	Value
Type code	MSSD
Contact durability	10
Type of mounting	On air solenoid valve with M3 central screw
Mounting position	Any
Product weight	38 g
Electrical connection	4-pin Socket Form A
Cable diameter	5.5 mm ... 8 mm
Nominal conductor cross section	0.5 mm ² ... 1 mm ²
Degree of protection	IP67 as per IEC 60529
Ambient temperature	-25 °C ... 90 °C
Housing material	PA
Housing colour	Black