

Plastic pipe PQ-PA-28X2,5X3000

Part number: 194594

FESTO



Data sheet

Feature	Value
Outside diameter	28 mm
Inside diameter	23 mm
Type code	PQ-PA
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Temperature of medium	-25 °C ... 75 °C
Ambient temperature	-25 °C ... 75 °C
Product weight by length	0.204 kg/m
Color	Black
Material of pneumatic tubing	PA