

Pneumatic muffler UO-1/4

Part number: 197584

FESTO



Data sheet

Feature	Value
Type code	UO
Mounting position	Any
Symbol	00991473
Operating pressure	0 bar ... 8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C ... 60 °C
Product weight	8 g
Pneumatic connection	G1/4
Cushioning insert material	PE
Material of screwed trunnion	PE
Note on materials	Free of copper and PTFE