

Spiral plastic tubing PUN-4X0,75-S-1-BL

Part number: 197588

FESTO



Data sheet

Feature	Value
Working length	1 m
Outside diameter	4 mm
Block length	0.284 m
Inside diameter	2.6 mm
Winding diameter	25 mm
Number of windings	45
Type code	PUN-S
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Ambient temperature	-35 °C ... 60 °C
Product weight	27 g
Pneumatic connection	For plug connection outside diameter 4 mm For barbed fitting, inside diameter 3 mm, with union nut For barbed fitting, inside diameter 3 mm
Color	Blue
Shore hardness	D 52 +/- 3
Note on materials	Free of copper and PTFE
Material of pneumatic tubing	TPE-U(PU)