

Spiral plastic tubing PUN-6X1-S-1-SW

Part number: 197605

FESTO



Data sheet

Feature	Value
Working length	1 m
Outside diameter	6 mm
Block length	0.344 m
Inside diameter	4 mm
Winding diameter	46 mm
Number of windings	23
Type code	PUN-S
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Ambient temperature	-35 °C ... 60 °C
Product weight	51 g
Pneumatic connection	For plug connection outside diameter 6 mm For barbed fitting, inside diameter 4 mm, with union nut For barbed fitting, inside diameter 4 mm
Color	Black
Shore hardness	D 52 +/- 3
Note on materials	Free of copper and PTFE
Material of pneumatic tubing	TPE-U(PU)