

Rotary distributor GF-3/8

Part number: 2095

FESTO



Data sheet

Feature	Value
Nominal width	15 mm
Type code	GF
Mounting position	Any
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Max. rotational speed	300 1/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Pneumatic connection 1	External thread G3/8
Pneumatic connection 2	Internal thread G3/8
Note on materials	RoHS-compliant