

Rod clevis SG-M16

Part number: 2676

FESTO



Data sheet

Feature	Value
Size	M16
Type code	SG
Based on norm	ISO 8140
Conforms to standard	DIN 71752
Threaded connection	Internal thread M16
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-40 °C ... 150 °C
Product weight	376 g
Note on materials	Free of copper and PTFE RoHS-compliant
Bolt material	Steel Galvanized
Clevis material	Steel Galvanized
Nut material	Steel Galvanized