

Distributor block FR-9-M3-B

Part number: 30981

FESTO



Data sheet

Feature	Value
Nominal width	2.5 mm
Type code	FR
Mounting position	Any
Operating pressure for entire temperature range	0 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-10 °C ... 80 °C
Product weight	15 g
No. of outlets	9
No. of supply lines	1
Pneumatic connection 1	Internal thread G1/8
Pneumatic connection 2	Internal thread M3
Note on materials	RoHS-compliant
Housing material	Aluminum Anodized