

Rod clevis SGA-M10X1,25

Part number: 32954

FESTO



Data sheet

Feature	Value
Size	M10x1.25
Radial deviation +/-	5 mm
Angle compensator +/-	120 deg
Type code	SGA
Mounting position	Any
Threaded connection	External thread M10x1.25
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-40 °C ... 150 °C
Product weight	129 g
Note on materials	Free of copper and PTFE RoHS-compliant
Bolt material	Steel Galvanized
Material of rod eye	Steel Galvanized
Fuse material	Spring steel, galvanized