

# Plug socket MSSD-V

Part number: 33295

FESTO



## Data sheet

Feature	Value
Type code	MSSD
Type of mounting	On air solenoid valve with M3 central screw
Mounting position	Any
Product weight	18 g
Electrical connection	3-pin Socket Socket, angled Form B as per DIN EN 175301-803 Rectangular design MSV
Cable fitting	Pg9
Cable diameter	6 mm ... 8 mm
Nominal conductor cross section	≤1.5 mm <sup>2</sup>
Degree of protection	IP65
Ambient temperature	-25 °C ... 90 °C
CE marking (see declaration of conformity)	As per EU low voltage directive
Housing material	Polymer
Housing colour	Black