

Sealing ring OL-1/8

Part number: 33840

FESTO



Data sheet

| Feature | Value |
|---|-------------------------------|
| Type code | OL |
| Based on norm | ISO 16030 |
| Pack size | 1 |
| Operating pressure for entire temperature range | -0.95 bar ... 30 bar |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS conformity | VDMA24364-B2-L |
| Ambient temperature | -40 °C ... 100 °C |
| Manual tightening at RT | yes |
| Nominal tightening torque | 6 Nm |
| Tolerance for nominal tightening torque | ± 20% |
| Note on materials | RoHS-compliant |