

Clevis foot LNG-50

Part number: 33892

FESTO



Data sheet

Feature	Value
Size	50
Type code	LNG
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-40 °C ... 80 °C
Product weight	281 g
Note on materials	Free of copper and PTFE RoHS-compliant
Mounting material	Tempered steel
Material of bearing	PA