

Clevis foot LNG-100

Part number: 33895

FESTO



Data sheet

Feature	Value
Size	100
Type code	LNG
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-40 °C ... 80 °C
Product weight	1141 g
Note on materials	Free of copper and PTFE RoHS-compliant
Mounting material	Spherulitic graphite iron
Material of bearing	PA