


Pneumatic timer

VZA-3-1/4

Part number: 3434

FESTO



Data sheet

Feature	Value
Type code	VZA
Symbol	00995725
Operating pressure	0 bar ... 10 bar
Standard nominal flow rate	600 l/min
Adjustable delay time	0 s ... 30 s
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Type of mounting	With through-hole
Pneumatic connection	G1/4 G1/8
Note on materials	RoHS-compliant