

Pressure gauge MA-50-16-1/4

Part number: 356759

FESTO



Data sheet

Feature	Value
Display range	0 bar ... 16 bar
Type code	MA
Symbol	00991463
Conforms to standard	EN 837-1
Pressure gauge nominal size	50
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Structural design	Bourdon tube pressure gauge
Type of mounting	Line installation
Operating medium	Inert gas Neutral liquids
Operating pressure	0 MPa ... 1.6 MPa
Operating pressure	0 bar ... 16 bar
Operating pressure	0 psi ... 232 psi
Intermittent load factor	0.66
Measurement accuracy class	2.5
Degree of protection	IP43
Temperature of medium	-20 °C ... 60 °C
Ambient temperature	-20 °C ... 60 °C
Note on materials	RoHS-compliant
Connection position	Centered on rear side
Pneumatic connection	G1/4
Materials in contact with the media	Brass
Material of screwed trunnion	Brass
Housing material	ABS
Inspection window material	PS
Housing colour	Black
Product weight	70 g

Feature	Value
Information on operating and pilot media	No acetylene No oxygen