

# Adaptive gripper finger DHAS-GF-80-U-BU

Part number: 3998964

FESTO



## Data sheet

Feature	Value
Size	80
Type code	DHAS
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
For use in the food industry	See supplementary material information
Ambient temperature	10 °C ... 50 °C
Product weight	13 g
Note on materials	Free of copper and PTFE RoHS-compliant
Clamping jaws material	TPE-U(PU)