


Swivel lever valve RW-3-M5

Part number: 4031

FESTO



Data sheet

| Feature | Value |
|--|--|
| Valve function | 3/2, closed, monostable |
| Actuation type | Mechanical |
| Standard nominal flow rate | 80 l/min |
| Pneumatic working port | M5 |
| Operating pressure | -0.95 bar ... 8 bar |
| Structural design | Piston seat |
| Nominal width | 2 mm |
| Type code | RW |
| Type of control | Direct |
| Symbol | 00991099 |
| Explosion prevention and protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Operating medium | Compressed air as per ISO 8573-1:2010 [:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Ambient temperature | -10 °C ... 60 °C |
| Actuating force | 14.5 N |
| Type of mounting | With through-hole |
| Pneumatic connection 1 | M5 |
| Pneumatic connection 2 | M5 |
| Seals material | NBR |
| Housing material | Die-cast zinc |