


Axial kit EAMM-A-T42-60P

Part number: 4133487

FESTO



Data sheet

Feature	Value
Nominal length	48 mm
Type code	EAMM-A
Mounting position	Any
Max. rotational speed	8000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	3.2 kgmm ²
Transferable torque	10 Nm
Product weight	330 g
Interface code, actuator	T42
Interface code, motor in	60P
Note on materials	RoHS-compliant