

# Solenoid coil MSFG-12

Part number: 4526

FESTO



## Data sheet

Feature	Value
Type code	MSFG
Mounting position	Any
Switching position indication	no
Min. pick-up time	10 ms
Duty cycle	100%
Coil characteristics	12 V DC: 4.1 W
Permissible voltage fluctuations	+/- 10 %
Degree of protection	IP65
Ambient temperature	-5 °C ... 40 °C
Max. tightening torque of socket	0.4 Nm
Product weight	55 g
Electrical connection	3-pin Plug flags with connection diagram as per Festo standard for MSSD-F
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Solenoid coil material	Duroplast Copper Steel
Material of winding	Copper