


Axial kit EAMM-A-V32-60P

Part number: 4608750

FESTO



Data sheet

Feature	Value
Nominal length	55.1 mm
Type code	EAMM-A
Mounting position	Any
Max. rotational speed	10000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	1.03 kgmm ²
Transferable torque	1.5 Nm
Product weight	210 g
Interface code, actuator	V32
Interface code, motor in	60P
Note on materials	RoHS-compliant