

Clevis foot LN-40

Part number: 5148

FESTO



Data sheet

| Feature | Value |
|----------------------------------|---|
| Size | 40 |
| Type code | LN |
| Based on norm | ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Ambient temperature | -40 °C ... 150 °C |
| Product weight | 192 g |
| Note on materials | Free of copper and PTFE RoHS-compliant |
| Mounting material | Tempered steel |