

Control element VAOH-P15-H13

Part number: 5196471

FESTO



Data sheet

Feature	Value
Stroke	20 mm
Piston diameter	50 mm
Type code	VAOH
Mounting position	Any
Position sensing	For proximity sensor
Operating pressure	≤1 bar
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Product weight	1350 g
Pneumatic connection 1	G1/8
Note on materials	Contains paint-wetting impairment substances RoHS-compliant