


Encoder cable NEBM-M12G8-E-10-N-R3G8

Part number: 5212315

FESTO



Data sheet

| Feature | Value |
|---|---|
| Type code | NEBM |
| Cable designation | Without label holder |
| Product weight | 570 g |
| Electrical connection 1, function | Field device end |
| Electrical connection 1, design | Round |
| Electrical connection 1, connection type | Socket |
| Electrical connection 1, cable outlet | Straight |
| Electrical connection 1, connection technology | M12x1 A-coded as per EN 61076-2-101 |
| Electrical connection 1, number of pins/wires | 8 |
| Electrical connection 1, occupied pins/wires | 8 |
| Electrical connection for input 1, connection pattern | 00992265 |
| Electrical connection 2, function | Control side |
| Electrical connection 2, design | Rectangular |
| Electrical connection 2, connection type | Plug |
| Electrical connection 2, cable outlet | Straight |
| Electrical connection 2, connection technology | RJ45 |
| Electrical connection 2, number of pins/wires | 8 |
| Electrical connection 2, occupied pins/wires | 8 |
| Electrical connection 2, connection pattern | 00995653 |
| DC operating voltage range | 0 V ... 30 V |
| Nominal operating voltage DC | 24 V |
| Operating voltage range AC | 0 V ... 30 V |
| Nominal operating voltage AC | 24 V |
| Cable length | 10 m |
| Cable characteristic | Suitable for energy chains |
| Bending radius, flexible cable installation | ≥48 mm |
| Cable diameter | 5.8 mm |
| Cable design | 1 x 4 x 0.15 mm ² + 4 x 1 x 0.34 mm ² Shielded |
| Nominal conductor cross section | 0.15 mm ² |
| Degree of protection | IP65 |
| Note on degree of protection | IP30 for Sub-D plug In mounted state |
| Ambient temperature | -40 °C ... 80 °C |

| Feature | Value |
|--|--------------------------|
| Ambient temperature with flexible cable installation | -5 °C ... 80 °C |
| CE marking (see declaration of conformity) | As per EU RoHS directive |
| Note on materials | RoHS-compliant |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| Material of cable sheath | TPE-U(PUR) |
| Color cable sheath | Black |