

# Plastic tubing PAN-V0-10X1,25-WS

Part number: 525480

FESTO



## Data sheet

Feature	Value
Outside diameter	12 mm
Bending radius relevant for flow rate	56 mm
Inside diameter	7.5 mm
Min. bending radius	34 mm
Type code	PAN-V0
Temperature-dependent operating pressure	-0.95 bar ... 12 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Mineral oil Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a>
Material fire test	UL94 V-0 (casing)
Ambient temperature	-30 °C ... 90 °C
Product weight by length	0.088 kg/m
Pneumatic connection	For plug connection outside diameter 10 mm
Color	White
Shore hardness	A 72 +/-4 D 57 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	PA12-P PVC-P