

Plastic tubing PAN-V0-8X1-GE

Part number: 525483

FESTO



Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	45 mm
Inside diameter	6 mm
Min. bending radius	24 mm
Type code	PAN-V0
Temperature-dependent operating pressure	-0.95 bar ... 12 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Mineral oil Water as per manufacturer's declaration at www.festo.com
Material fire test	UL94 V-0 (casing)
Ambient temperature	-30 °C ... 90 °C
Product weight by length	0.065 kg/m
Pneumatic connection	For plug connection outside diameter 8 mm
Color	Yellow
Shore hardness	A 72 +/-4 D 57 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	PA12-P PVC-P