

Quick coupling socket KD2-CK-4

Part number: 531622

FESTO



Data sheet

Feature	Value
Nominal width	2.9 mm
Type code	KD2
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Standard nominal flow rate	123 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 80 °C
Product weight	16 g
Pneumatic connection 1	CK-4
Note on materials	RoHS-compliant