

# Quick coupling plug KS4-1/2-A

Part number: 531676

FESTO



## Data sheet

Feature	Value
Nominal width	7.85 mm
Type code	KS4
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Standard nominal flow rate	1301 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Nominal tightening torque	32.5 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	55 g
Pneumatic connection 1	External thread G1/2
Note on materials	RoHS-compliant