

Sealing ring OK-3/8

Part number: 531773

FESTO



Data sheet

Feature	Value
Type code	OK
Based on norm	ISO 16030
Pack size	1
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-10 °C ... 60 °C
Manual tightening at RT	yes
Nominal tightening torque	12.5 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	0.44 g
Note on materials	Free of copper and PTFE RoHS-compliant