


Push-in T-fitting QBMT-1/8-1/8-U-M

Part number: 533251

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	2.489 mm
Type code	QBMT
Type of seal on screwed trunnion	Coating
Operating pressure for entire temperature range	-0.951 bar ... 9.997 bar
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	0 °C ... 60 °C
Product weight	8.193 g
Releasing ring color	Gray
Note on materials	RoHS-compliant
Housing material	PBT
Material of threaded seal	NBR
Releasing ring material	POM
Material of tube retaining claw	High-alloy stainless steel