

Ball valve VAPB-3/4-F-40-F03

Part number: 534305

FESTO



Data sheet

| Feature | Value |
|---|---------------------------------|
| Type code | VAPB |
| Structural design | 2-way ball valve |
| Actuation type | Mechanical |
| Sealing principle | Soft |
| Mounting position | Any |
| Type of mounting | Line installation |
| Fitting connection | Rp3/4 |
| Switching position indication | Slot direction = flow direction |
| Flange hole pattern | F03 |
| Nominal width DN | 20 |
| Flow direction | Reversible |
| Nominal pressure of fitting PN | 40 |
| Breakaway torque at differential pressure, nominal pressure, fitting PN | 6 Nm |

| Feature | Value |
|--|---|
| Breakaway torque at 10 bar differential pressure | 5.1 Nm |
| Based on norm | ISO 5211 |
| Symbol | 00991458 |
| Medium | Compressed air as per ISO 8573-1:2010 [:-:-] Inert gas Water Neutral liquids |
| Temperature of medium | -20 °C ... 150 °C |
| Flow rate Kv | 41 m ³ /h |
| Note on materials | Contains paint-wetting impairment substances RoHS-compliant |
| Housing material | Brass Nickel-plated |
| Material number of housing | CW617N |
| Seals material | HNBR PTFE |
| Ball material | Brass Hard-chrome-plated |
| Material number for ball | CW617N |
| Shaft material | Brass |
| Material number for shaft | CW614N |
| Product weight | 500 g |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |