


Vacuum filter VAF-PK-3

Part number: 535883

FESTO



Data sheet

Feature	Value
Nominal width	2 mm
Type code	VAF
Mounting position	Any
Grade of filtration	50 µm
Symbol	00991483
Operating pressure	-0.95 bar ... 0 bar
Information on operating pressure	Only for use in open vacuum systems
Flow rate at negative pressure = -0.75 bar	50.8 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-:]
Ambient temperature	0 °C ... 40 °C
Product weight	4 g
Type of mounting	Line installation
Pneumatic connection	PK-3 with union nut
Material of union nut	POM
Note on materials	RoHS-compliant
Compressed air filter material	Fabric PA
Housing material	PA
Ejector pulse suitability	≤8 bar