

Module connector MS12-MV

Part number: 537134

FESTO



Data sheet

Feature	Value
Size	12
Type code	MS12-MV
Series	MS
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Storage temperature	-10 °C ... 60 °C
Temperature of medium	-10 °C ... 60 °C
Product weight	500 g
Note on materials	Free of copper and PTFE RoHS-compliant
Seals material	NBR
Plate material	Die-cast aluminum
Material of screws	Steel