


Clevis flange SNCL-16-R3

Part number: 537795

FESTO



Data sheet

Feature	Value
Size	16
Type code	SNCL
Based on norm	ISO 21287
Variants	High corrosion protection
Corrosion resistance class (CRC)	3 - High corrosion stress
Ambient temperature	-40 °C ... 90 °C
Product weight	21 g
Note on materials	Free of copper and PTFE RoHS-compliant
Mounting material	Wrought aluminum alloy With protective coating
Material of bearing	Polymer
Material of screws	High-alloy stainless steel