

# Rotary distributor GF-1/8-2

Part number: 539287

FESTO



## Data sheet

Feature	Value
Nominal width	6 mm
Type code	GF
Mounting position	Any
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Standard nominal flow rate 1.1-2.1	720 l/min
Standard nominal flow rate 1.2-2.2	1050 l/min
Max. rotational speed	300 1/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 80 °C
Nominal tightening torque	1.22 Nm
Tolerance for nominal tightening torque	± 20%
Pneumatic connection 1	G1/8
Pneumatic connection 2	G1/8