

Rotary distributor GF-1/4-1/8

Part number: 539291

FESTO



Data sheet

Feature	Value
Nominal width	8 mm
Type code	GF
Mounting position	Any
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Standard flow rate 1-2.1 (6->0)	1730 l/min
Standard flow rate 1-2.X open (6->0)	4050 l/min
Max. rotational speed	3000 1/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 80 °C
Nominal tightening torque	1.65 Nm
Tolerance for nominal tightening torque	± 20%
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/8