

Plug socket MSSD-V-M16

Part number: 539713

FESTO



Data sheet

Feature	Value
Type code	MSSD
Contact durability	50
Type of mounting	On air solenoid valve with M3 central screw
Mounting position	Any
Product weight	35 g
Electrical connection	3-pin Socket, angled Form B as per DIN EN 175301-803 Rectangular design
Cable fitting	M16
Approved cable diameter	6 mm ... 8 mm
Connection cross section	0.75 mm ²
Degree of protection	IP65 as per IEC 60529
Ambient temperature	-20 °C ... 115 °C
Housing material	PA-reinforced
Seals material	HNBR