


Soft start valve MS12-DL-G

Part number: 541497

FESTO



Data sheet

Feature	Value
Type code	MS12-DL
Exhaust air function	With flow control option
Actuation type	Pneumatic
Mounting position	Any
Manual override	None
Structural design	Piston seat
Reset method	Mechanical spring
Type of control	Direct
Pilot air supply port	Internal
Flow direction	Non-reversible
Symbol	00991513
Valve function	2/2
Operating pressure	2 bar ... 20 bar
Standard nominal flow rate	25000 l/min ... 42000 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	3600 g
Type of mounting	Optionally: Line installation With accessories
Pneumatic connection 1	Battery module
Pneumatic connection 2	Battery module
Note on materials	Free of copper and PTFE
Seals material	NBR
Housing material	Die-cast aluminum