


Signal conditioner SVE4-US-R-HM8-2N-M8

Part number: 544220

FESTO



Data sheet

| Feature | Value |
|--|--|
| Type code | SVE4 |
| Symbol | 00991961 |
| Certification | RCM compliance mark c UL us - Listed (OL) |
| UL-ambient temperature | -20 °C ... 60 °C |
| CE marking (see declaration of conformity) | As per EU EMC directive |
| Note on materials | Free of copper and PTFE |
| Signal range | 0 - 10 V +/-0.3 V |
| Ambient temperature | -20 °C ... 70 °C |
| Switching output | 2xNPN |
| Switching function | Freely programmable |
| Switching element function | Switchable |
| Short-circuit protection | Pulsed |
| Overload protection | Available |
| DC operating voltage range | 10 V ... 30 V |
| Electrical connection, input | Socket M8x1 4-pin as per EN 60947-5-2 |
| Electrical connection, output | Plug M8x1 4-pin as per EN 60947-5-2 |
| Product weight | 19 g |
| Housing material | ABS |
| Setting options | Teach-in |
| Degree of protection | IP65 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |