


Vertical pressure supply plate VABF-S3-2-P1A3-G18

FESTO

Part number: 544435



Data sheet

Feature	Value
Width	18 mm
Type code	VABF
Based on norm	ISO 15407-1
Mounting position	Any
Pneumatic vertical stacking	Alternative pressure supply for 1
Symbol	00991883
Operating pressure	-0.9 bar ... 10 bar
Standard nominal flow rate	500 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C ... 50 °C
Product weight	146 g
Vertical stacking mounting type	On manifold sub-base On individual sub-base
Note on materials	RoHS-compliant
Housing material	Die-cast aluminum