


Basic valve LFR-D-5M-MIDI-A

Part number: 546462

FESTO



Data sheet



Feature	Value
Size	Midi
Type code	LFR
Series	D
Actuator lock	Rotary knob with detent
Mounting position	Vertical +/- 5°
Grade of filtration	5 µm
Condensate drain	Fully automatic
Structural design	Filter regulator without pressure gauge
Max. condensate volume	42.983 ml
Bowl guard	Metal bowl guard
Symbol	00991584
Pressure gauge	G1/4 prepared
Operating pressure	1.931 bar ... 12.411 bar
Pressure regulation range	0.476 bar ... 12.411 bar
Max. pressure hysteresis	0.207 bar
Standard nominal flow rate	10677.97 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:9:-] Inert gas
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Storage temperature	-10 °C ... 60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gas
Temperature of medium	5 °C ... 60 °C
Ambient temperature	5 °C ... 60 °C
Product weight	893.025 g
Type of mounting	Optionally: Line installation With accessories
Note on materials	Free of copper and PTFE RoHS-compliant
Housing material	Die-cast zinc
Material of bowl	PC