

# Solenoid coil MH-2-230VAC-PA

Part number: 549908

FESTO



## Data sheet

| Feature                                     | Value  |
|---|--|
| Type code                                   | MH   |
| Mounting position                           | Any  |
| Switching position indication               | no   |
| Min. pick-up time                           | 12 ms  |
| Duty cycle                                  | 100%   |
| Power factor cos {phi}                      | 0.7  |
| Coil characteristics                        | 230 V AC: 14.0 VA                            |
| Permissible frequency fluctuations          | +/- 10%                                      |
| Permissible voltage fluctuations            | +/- 10 %                                     |
| CE marking (see declaration of conformity)  | As per EU low voltage directive              |
| Degree of protection                        | IP65   |
| Ambient temperature                         | -20 °C ... 50 °C                             |
| Max. tightening torque of pneumatic fitting | 2 Nm   |
| Product weight                              | 150 g  |
| Electrical connection                       | as per DIN EN 175301-803                     |
| Type of mounting                            | With lock nut                                |
| Note on materials                           | Contains paint-wetting impairment substances |
| Solenoid coil material                      | Duroplast<br>Copper<br>Steel                 |
| Material of winding                         | Copper                                       |