

Plug socket with cable KMYZ-4-2,5-B-EX

Part number: 550481

FESTO



Data sheet

Feature	Value
Type code	KMYZ
Maritime classification	See certificate
Type of mounting	On air solenoid valve with M2 central screw
Mounting position	Any
Product weight	34.5 g
Electrical connection	Socket, angled Cable Ractangular design MSZB
DC operating voltage range	3 V ... 36 V
Nominal operating voltage DC	24 V
Protective earth connection	Not available
Cable length	2.5 m
Cable characteristic	Standard
Cable design	2 x 0.35 mm ²
Degree of protection	IP50
Ambient temperature	-10 °C ... 50 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	1 - Low corrosion stress
Material of cable sheath	PVC
Housing material	PA
Material of pin contacts	Bronze