

Plastic tubing PLN-16X2-SI

Part number: 558216

FESTO



Data sheet

Feature	Value
Outside diameter	16 mm
Bending radius relevant for flow rate	95 mm
Inside diameter	12 mm
Min. bending radius	55 mm
Type code	PLN
Temperature-dependent operating pressure	-0.95 bar ... 14 bar
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-] Water as per manufacturer's declaration at www.festo.com
For use in the food industry	See supplementary material information
Ambient temperature	-30 °C ... 80 °C
Product weight by length	0.082 kg/m
Pneumatic connection	For plug connection outside diameter 16 mm
Color	Silver
Note on materials	Free of copper and PTFE RoHS-compliant
Material of pneumatic tubing	PE