

Plastic tubing PLN-4X0,75-RT

Part number: 558217

FESTO



Data sheet

Feature	Value
Outside diameter	4 mm
Bending radius relevant for flow rate	25 mm
Inside diameter	2.9 mm
Min. bending radius	12 mm
Type code	PLN
Temperature-dependent operating pressure	-0.95 bar ... 14 bar
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com
For use in the food industry	See supplementary material information
Ambient temperature	-30 °C ... 80 °C
Product weight by length	0.0056 kg/m
Pneumatic connection	For plug connection outside diameter 4 mm For barbed fitting, inside diameter 3 mm, with union nut For barbed fitting, inside diameter 3 mm
Color	Red
Note on materials	Free of copper and PTFE RoHS-compliant
Material of pneumatic tubing	PE