

Plastic tubing PLN-12X1,75-RT

Part number: 558221

FESTO



Data sheet

Feature	Value
Outside diameter	12 mm
Bending radius relevant for flow rate	65 mm
Inside diameter	8.4 mm
Min. bending radius	23 mm
Type code	PLN
Temperature-dependent operating pressure	-0.95 bar ... 14 bar
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-] Water as per manufacturer's declaration at www.festo.com
For use in the food industry	See supplementary material information
Ambient temperature	-30 °C ... 80 °C
Product weight by length	0.054 kg/m
Pneumatic connection	For plug connection outside diameter 12 mm
Color	Red
Note on materials	Free of copper and PTFE RoHS-compliant
Material of pneumatic tubing	PE