

Push-in Y-connector NPQM-Y-Q10-E-P10

Part number: 558801

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal width | 9.5 mm |
| Type code | NPQM-Y |
| Structural design | Push-pull principle |
| Operating pressure for entire temperature range | -0.95 bar ... 16 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Ambient temperature | -20 °C ... 70 °C |
| Product weight | 62.7 g |
| Pneumatic connection 1 | for pneumatic tubing outside diameter 10 mm |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 10 mm |
| Note on materials | RoHS-compliant |
| Housing material | Brass, nickel-plated |
| Material of tubing seal | NBR |