


# Axial kit EAMM-A-L38-87A

Part number: 560680

FESTO



## Data sheet

Feature	Value
Type code	EAMM-A
Mounting position	Any
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Transferable torque	4.4 Nm
Product weight	480 g
Interface code, actuator	L38
Interface code, motor in	87A
Note on materials	RoHS-compliant