

Manifold subbase VABV-S2-2S-N12-T2

Part number: 560843

FESTO



Data sheet

Feature	Value
Width dimension	59 mm
Type code	VABV
Valve terminal type	44
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
CE marking (see declaration of conformity)	As per EU low voltage directive
Corrosion resistance class (CRC)	0 - No corrosion stress
Product weight	610 g
Pneumatic connection 2	1/2 NPT
Pneumatic connection 4	1/2 NPT
Note on materials	RoHS-compliant
Plate material	Die-cast aluminum