


End plate VMPAL-EPL-SD25

Part number: 560938

FESTO



Data sheet

Feature	Value
Width	43 mm
Length	107.3 mm
Type code	VMPAL
Max. no. of valve positions	24
Valve manifold design	Valve sizes can be mixed
Max. no. of solenoid coils	24
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Pilot pressure MPa	0.3 MPa ... 0.8 MPa
Pilot pressure	3 bar ... 8 bar
Nominal operating voltage DC	24 V
Corrosion resistance class (CRC)	3 - High corrosion stress
Degree of protection	IP67
Note on degree of protection	In mounted state With VPMAL-KM accessories
Ambient temperature	-5 °C ... 50 °C
Product weight	190 g
Electrical connection 1, function	Multi-pin
Electrical connection 1, connection type	Plug
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	25
Electrical connection for input 1, connection pattern	00995643
Note on materials	RoHS-compliant
End plate material	Die-cast aluminum PA-reinforced