

# Plate VMPAL-EG-QS3/8"

Part number: 560959

FESTO



## Data sheet

Feature	Value
Width	20.5 mm
Length	107.3 mm
Type code	VMPAL
Integrated function	Ducted exhaust air
Valve manifold design	Valve sizes can be mixed
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Pressure regulation range	0.5 bar ... 5 bar
Inlet pressure 1	0.5 bar ... 10 bar
Corrosion resistance class (CRC)	3 - High corrosion stress
Ambient temperature	-5 °C ... 50 °C
Product weight	60 g
Pneumatic port 3/5 combined	For pneumatic tubing outside diameter 3/8"
Note on materials	RoHS-compliant
Plate material	PA